

FF-FIMT 4X 54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

Type	FF-FIMT 4X 54
Order No.	2556790000
Version	Filter mat, IP54, white
GTIN (EAN)	4050118567410
Qty.	5 pc(s).

FF-FIMT 4X 54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	216 mm
Height	216 mm
Net weight	13.2 g

Width (inches)	8.504 inch
Height (inches)	8.504 inch

General data

Colour	white
Operating temperature range	-40...55 °C
Type of mounting	Snap-on

Filter class	G 4
Protection class (UL)	Type 12
With filter	Yes

Classifications

ETIM 6.0	EC002513
eClass 9.1	27-18-07-06

ETIM 7.0	EC002513
eClass 10.0	27-18-07-06

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Operating instructions
--------------------	--