

FH-TCO 400W 230V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

Type	FH-TCO 400W 230V
Order No.	2558000000
Version	Heating panel fan, IP20, silver
GTIN (EAN)	4050118568646
Qty.	1 pc(s).

FH-TCO 400W 230V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	85 mm	Width (inches)	3.346 inch
Height	226.5 mm	Height (inches)	8.917 inch
Depth	104 mm	Depth (inches)	4.094 inch
Net weight	1,200 g		

General data

Continuous heat output at 10°C	400 W	Inrush current	max. 1.8 A
Operating temperature range	-40...70 °C	Operating voltage	230 V AC
Type of connection	Spring contact	Type of mounting	Rail
With room thermostat	No		

Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
eClass 9.1	27-18-07-10	eClass 10.0	27-18-07-10

Approvals

Approvals



ROHS

Conform

DownloadsEngineering Data [STEP](#)