

FH-TH 1200W 230V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

Type	FH-TH 1200W 230V BK
Order No.	2558160000
Version	Heating panel fan, IP20, black
GTIN (EAN)	4050118568813
Qty.	1 pc(s).

FH-TH 1200W 230V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	88 mm	Width (inches)	3.465 inch
Height	142 mm	Height (inches)	5.591 inch
Depth	139 mm	Depth (inches)	5.472 inch
Net weight	790 g		

General data

Continuous heat output at 10°C	1,200 W	Inrush current	max. 31 A
Operating temperature range	-40...70 °C	Operating voltage	230 V AC
Temperature setting range, max.	40 °C	Temperature setting range, min.	-20 °C
Type of connection	Spring contact	Type of mounting	Rail, Screw mounting
With room thermostat	Yes		

Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
eClass 9.1	27-18-07-10	eClass 10.0	27-18-07-10

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity EU Declaration of Conformity
Engineering Data	STEP
User Documentation	Operating instructions