

REF 600 33 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

Type	REF 600 33 GY
Order No.	2557850000
Version	Exhaust filter, IP33, grey
GTIN (EAN)	4050118568493
Qty.	1 pc(s).

REF 600 33 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	436 mm	Width (inches)	17.165 inch
Height	436 mm	Height (inches)	17.165 inch
Depth	106 mm	Depth (inches)	4.173 inch
Net weight	2,500 g		

General data

Colour	grey	EMC version	No
Fan type	Roof fan	Height of installation cut-outs	291 mm
Mounting depth	34 mm	Mounting height	72 mm
Operating temperature range	-15...55 °C	Type of mounting	Snap-on
Width of installation cut-outs	291 mm	With filter	No

Classifications

ETIM 6.0	EC002513	ETIM 7.0	EC002513
eClass 9.1	27-18-07-06	eClass 10.0	27-18-07-06

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	STEP
User Documentation	Installation- and operating instructions