

RH-CBCO 150W 110-250V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

Type	RH-CBCO 150W 110-250V
Order No.	2557950000
Version	Radiant heating panel, 110 V, 250 V, silver
GTIN (EAN)	4050118568592
Qty.	1 pc(s).

RH-CBCO 150W 110-250V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	70 mm	Width (inches)	2.756 inch
Height	250 mm	Height (inches)	9.842 inch
Depth	50 mm	Depth (inches)	1.969 inch
Net weight	510 g		

General data

Continuous heat output at 10°C	150 W	Inrush current	max. 7.5 A
Operating temperature range	-40...70 °C	Supply voltage, max.	250 V
Supply voltage, min.	110 V	Type of connection	Pre-assembled cable
Type of mounting	Rail	With room thermostat	No

Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
eClass 9.1	27-18-07-10	eClass 10.0	27-18-07-10

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	STEP