

**WIL-BM-JP-M12-3.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Motion detector for the WIL-LED luminaire in the Jackpac® housing With 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | WIL-BM-JP-M12-3.0U         |
| Order No.  | <a href="#">2537710000</a> |
| GTIN (EAN) | 4050118549164              |
| Qty.       | 1 pc(s).                   |

## WIL-BM-JP-M12-3.0U

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Width      | 51 mm | Width (inches)  | 2.008 inch |
| Height     | 23 mm | Height (inches) | 0.906 inch |
| Depth      | 36 mm | Depth (inches)  | 1.417 inch |
| Net weight | 40 g  |                 |            |

## Temperatures

|                             |            |                             |        |
|-----------------------------|------------|-----------------------------|--------|
| Operating temperature, max. | 60 °C      | Operating temperature, min. | -20 °C |
| Operating temperature       | -20 - 60°C |                             |        |

## Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

## Cable technical specifications

|                |     |                    |                      |
|----------------|-----|--------------------|----------------------|
| Cable Material | PUR | Sheathing colour   | black                |
| Cable length   | 3 m | Core cross-section | 0.34 mm <sup>2</sup> |

## Connection data

|                   |        |                   |                                   |
|-------------------|--------|-------------------|-----------------------------------|
| Coding            | A      | Connection thread | M12                               |
| Tightening torque | 0.8 Nm | Wiring            | PIN 4: + (black), PIN 3: - (blue) |

## Electric data

|                      |         |               |         |
|----------------------|---------|---------------|---------|
| Rated voltage (text) | 24 V DC | Rated current | < 3.0 A |
|----------------------|---------|---------------|---------|

## General technical data

|                   |      |
|-------------------|------|
| Protection degree | IP20 |
|-------------------|------|

## Classifications

|          |          |          |          |
|----------|----------|----------|----------|
| ETIM 6.0 | EC002955 | ETIM 7.0 | EC002955 |
|----------|----------|----------|----------|

## Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## WIL-BM-JP-M12-3.0U

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

