

**WIL-BM-SK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | WIL-BM-SK                  |
| Order No.  | <a href="#">2537720000</a> |
| GTIN (EAN) | 4050118549157              |
| Qty.       | 1 pc(s).                   |

**WIL-BM-SK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Width      | 76 mm | Width (inches)  | 2.992 inch |
| Height     | 33 mm | Height (inches) | 1.299 inch |
| Depth      | 44 mm | Depth (inches)  | 1.732 inch |
| Net weight | 35 g  |                 |            |

**Temperatures**

|                             |            |                             |        |
|-----------------------------|------------|-----------------------------|--------|
| Operating temperature, max. | 60 °C      | Operating temperature, min. | -20 °C |
| Operating temperature       | -20 - 60°C |                             |        |

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**Connection data**

|                   |          |        |                                   |
|-------------------|----------|--------|-----------------------------------|
| Connection thread | Terminal | Wiring | PIN 4: + (black), PIN 3: - (blue) |
|-------------------|----------|--------|-----------------------------------|

**Electric data**

|                      |         |               |         |
|----------------------|---------|---------------|---------|
| Rated voltage (text) | 24 V DC | Rated current | < 6.0 A |
|----------------------|---------|---------------|---------|

**General technical data**

|                   |      |
|-------------------|------|
| Protection degree | IP20 |
|-------------------|------|

**Classifications**

|          |          |          |          |
|----------|----------|----------|----------|
| ETIM 6.0 | EC002955 | ETIM 7.0 | EC002955 |
|----------|----------|----------|----------|

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## WIL-BM-SK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Drawings

