



2-Way Outlet Shapes, Breakout Boots


Helashrink 200 Series, in line, low voltage

Features and benefits

- Easy, time-saving insulation of cable branch point where it splits into single wires
- Adhesive to relieve mechanical tension in cable harnesses



a: Expanded form (supplied)



b: Fully recovered form (after heating)



223-2 supplied / fully recovered.

TYPE	ØH min. a	ØH max. b	ØJ min. a	ØJ max. b	P ± 10 %	R ± 10 %	HW ± 20 %	JW ± 20 %	S nom.	Article-No.
216-3-B8W	21.0	9.4	9.0	2.8	76.5	20.0	1.6	1.6	14.0	402-16039
223-2-B8W	33.0	9.4	17.5	4.1	94.0	30.0	1.5	1.2	20.0	402-23058
218-2-B8W	49.0	22.9	20.0	7.6	119	34.0	3.2	3.2	30.0	402-18051


All dimensions in mm. Subject to technical changes.

4-Way Outlet Shapes, Breakout Boots


Helashrink 400 Series, in line, low voltage

Features and benefits

- Easy, time-saving insulation of cable branch point where it splits into single wires
- Made of tough, cross-linked, Polyolefin
- Adhesive is applied to relieve mechanical tension in cable harnesses



a: Expanded form (supplied)



b: Fully recovered form (after heating)



400 series supplied / fully recovered.

TYPE	ØH min. a	ØH max. b	ØJ min. a	ØJ max. b	P ± 10 %	R ± 10 %	HW ± 20 %	JW ± 20 %	S nom.	Article-No.
442-1-B8WM250	28.0	9.0	9.0	1.8	78.0	17.0	2.7	2.0	20.0	404-42009
408-2-B8W2	35.0	12.0	15.0	3.0	95.0	24.0	2.5	2.0	22.0	404-08022
418-4-B8W2	60.0	22.9	30.0	6.4	202.0	38.1	4.1	3.3	38.1	404-18020

All dimensions in mm. Subject to technical changes.