

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

Part Number: 0936040058

**Status:** **Active**

**Overview:** GWconnect Heavy Duty Connectors (HDC)

**Description:** GWconnect Enclosure, Die-cast Aluminum, S-8000 Series, with External Mounting Flanges, 101 x 101 x 58mm Outside Dimensions, Sandblasted

## Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

## General

|                  |                                                                                                |
|------------------|------------------------------------------------------------------------------------------------|
| Product Family   | Industrial Connectors / Enclosures                                                             |
| Series           | 93604                                                                                          |
| IP Rating        | IP66, IP69                                                                                     |
| Overview         | <u>GWconnect Heavy Duty Connectors (HDC)</u>                                                   |
| Product Category | Die-cast Enclosures                                                                            |
| Product Name     | GWconnect                                                                                      |
| Standard         | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 60670-1, EN 62208, EN-60670-22, NMX-J235/1-2 |
| Type             | Sandblasted                                                                                    |
| UPC              | 887191870830                                                                                   |

## Physical

|                               |                   |
|-------------------------------|-------------------|
| Internal Dimensions           | 91 x 91 x 53mm    |
| Material - Enclosure          | Die-cast Aluminum |
| Mounting Style                | External Flanges  |
| Net Weight                    | 263.500/g         |
| Outside Dimensions            | 101 x 101 x 58mm  |
| Packaging Type                | Carton            |
| Temperature Range - Operating | -40° to +125°C    |

## Material Info

Engineering Number 8000.6281.0



Series image - Reference only

## EU ELV

**Not Relevant**

## EU RoHS

## Compliant

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

### Halogen-Free

## Status

## Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

## RoHS Phthalates

## China RoHS

Green Image

Not Relevant

Not Contained

### Search Parts in this Series

93604 Series

### Use With

DIN-rails, mounting supports, fixing screws,  
metal plates, and ground terminals

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**