

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936040070

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect Enclosure, Die-cast Aluminum, S-8000 Series, with External Mounting Flanges, 189 x 167 x 80mm Outside Dimensions, Grey RAL 7037

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93604</u>
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Die-cast Enclosures
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 60670-1, EN 62208, EN-60670-22, NMX-J235/1-2
Type	ATEX
UPC	887191871455

Physical

Enclosure Coating	Polyester Powder
Enclosure Color	Grey RAL 7037
Internal Dimensions	178 x 155 x 74mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	External Flanges
Net Weight	848.000/g
Outside Dimensions	189 x 167 x 80mm
Packaging Type	Carton
Temperature Range - Operating	-20° to +85°C

Material Info

Engineering Number 8000.6294.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

93604 Series

Use With

DIN-rails, mounting supports, fixing screws,
metal plates, and ground terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION