

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936040204](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 160 x 160 x 90mm Outside Dimensions, Sandblasted

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93604
IP Rating	IP66, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Die-cast Enclosures
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 62208, NEMA ICS5, NEMA250, NMX-J235/1-2
Type	Sandblasted
UPC	887191879291
Physical	
Internal Dimensions	151 x 151 x 84mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	Internal Through Holes
Net Weight	1595.000/g
Outside Dimensions	160 x 160 x 90mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +125°C
Material Info	
Engineering Number	8100.8219.0



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93604](#) Series

Use With
DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION