

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936040266

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 100 x 100 x 80mm Outside Dimensions, Black RAL 9005



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93604
IP Rating	IP66, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Die-cast Enclosures
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 62208, NEMA ICS5, NEMA250, NMX-J235/1-2
Type	STD
UPC	887191883410
Physical	
Enclosure Coating	Polyester Powder
Enclosure Color	Black RAL 9005
Internal Dimensions	92 x 92 x 73mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	Internal Through Holes
Net Weight	615.000/g
Outside Dimensions	100 x 100 x 80mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +125°C
Material Info	
Engineering Number	8100.8315.1

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93604 Series

Use With

DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION