

DYMO®

LabelWriter™ 450 Duo



PAPER AND PLASTIC LABEL PRINTER FOR PC AND MAC®

- Add versatility to your label printing — print both Authentic DYMO® LW labels at 300dpi and Authentic DYMO® D1 labels at 180dpi in a variety of sizes and colors
- Save time - print up to 71 labels per minute*
- Create custom labels from 60+ label styles and layouts
- Thermal printing technology - no ink or toner needed
- Customize and print address, shipping, file folder and barcode labels, plus name badges from text in Microsoft® Word, Excel® Outlook®, Google Contacts® with DYMO® Connect for Desktop Software
- For even more features, download DYMO® Connect for Desktop Software

* 4-line address label



Single Unit Includes:

- LabelWriter 450 Duo
- D1 Starter Label Cassette, 24mm x 3m Black on White
- Address Labels Starter Roll
- Power Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- 2 + 1 - Year Limited Warranty**



Quick Specs

Unit Dimensions (H x W x L)	140 x 197 x 183 mm
Weight	2.4 Kg
Mac®/PC Compatible	Yes via DYMO® Connect for Desktop Software
Max Label Width	62mm LW and 24mm D1
Resolution	600 x 300 dpi on LW 180 dpi on D1 Labels
Printing System	LW: Direct Thermal D1: Thermal Transfer
Print Speed	71 labels/minute
Barcodes	Yes
Power Source	Adapter Power Cable
Networking	Print Server Sold Separately
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
S0838920	LabelWriter 450Duo	Unit	14.9	29.9	22.5	1	3501170838921	
Accessories (www.dymo.com)								
931160	Switching Adapter	Unit	29.7	24.2	16.3	1	-	

** +1 year if registered on the DYMO® website

www.DYMO.com

D1 Standard Polyester Labels

For hundreds of tasks around the office or home office, such as filing, storage and asset tracking.

Temperature rating: -18°C to 90°C



D1 STANDARD LABELS (3 m)	6 mm	9 mm	12 mm	19 mm	24 mm
ABC	-	-	2084349	-	-
ABC	-	-	2084401	-	-
D1 STANDARD LABELS (7 m)	6 mm	9 mm	12 mm	19 mm	24 mm
ABC	S0720780	S0720680	S0720530	S0720830	S0720930
ABC	S0720770	S0720670	S0720500	S0720820	S0720920
ABC	S0720790	S0720730	S0720580	S0720880	S0720980
ABC	-	S0720710	S0720560	S0720860	-
ABC	-	S0720740	S0720590	S0720890	-
ABC	-	S0720720	S0720570	S0720870	S0720970
ABC	-	-	S0720610	S0720910	S0721010
ABC	-	S0720690	S0720540	S0720840	-
ABC	-	-	S0720510	-	-
ABC	-	-	S0720600	-	-
ABC	-	S0720700	S0720550	S0720850	-
ABC	-	-	S0720520	-	-
D1 STANDARD MULTIPACKS (7 m)	6 mm	9 mm	12 mm	19 mm	24 mm
ABC	-	2093096	2093097	2093098	-



D1 Durable Vinyl Labels

Industrial strength adhesive helps to ensure labels stay stuck to a variety of surfaces.

Temperature rating: -40°C to 80°C

D1 DURABLE LABELS (3 m)	12 mm
ABC	1978366
ABC	1978365
ABC	1978367
D1 DURABLE LABELS (5.5 m)	12 mm
ABC	1978364



D1 Permanent Polyester Labels

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins and more.

Temperature rating: -40°C to 150°C*

D1 PERMANENT POLYESTER (5.5 m)	12 mm	19mm
ABC	S0718060	S0718050

*depends on surface



D1 Flexible Nylon Labels

Specifically designed for curved surfaces and wire and cable marking.

Temperature rating: -40°C to 60°C

D1 FLEXIBLE NYLON (3.5 m)	12 mm	19 mm
ABC	S0718040	S0718070



The DYMO® high quality labels are made in Belgium



© 2019 Newell Brands

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



LW Standard labels

Hassle-free labels for all your mailing, shipping and organizational needs.

Label Type	Description	Code #	Size (mm)	Rolls/Box	Labels/Roll	Adhesive	Material
Mailing	Standard Address Labels	S0722370	28 x 89	2	130	Permanent	Paper
	Standard Address Labels	S0722360	28 x 89	24	130	Permanent	Paper
	Standard Address Labels	2093091	28 x 89	12	130	Permanent	Paper
	Assorted Colour Labels	S0722380	28 x 89	4	130	Permanent	Paper
	Large Address Labels	S0722400	36 x 89	2	260	Permanent	Paper
	Large Address Labels	S0722390	36 x 89	24	260	Permanent	Paper
	Large Address Labels	2093093	36 x 89	12	240	Permanent	Paper
	Large Address Labels	S0722410	36 x 89	1	260	Permanent	Transparent Plastic
	Large Return Address Labels	S0722520	25 x 54	1	500	Permanent	Paper
Shipping	Shipping / Name Badge Labels	S0722430	54 x 101	1	220	Permanent	Paper
	High Capacity Shipping Labels	S0947420	102 x 59	2	575	Permanent	Paper
	Shipping / Name Badge Labels	2093092	54 x 101	6	220	Permanent	Paper
	Shipping / Name Badge Labels	S0722420	54 x 101	12	220	Permanent	Paper
	Extra Large Shipping Labels	S0904980	104 x 159	1	220	Permanent	Paper
Multi-Purpose	Multi-Purpose Labels	S0722530	13 x 25	1	1000	Removable	Paper
	Square Multi-Purpose Labels	S0929120	25 x 25	1	750	Removable	Paper
	Multi-Purpose Labels	S0722550	19 x 51	1	500	Removable	Paper
	Multi-Purpose Labels	S0722540	32 x 57	1	1000	Removable	Paper
	Large Multi-Purpose Labels	S0722440	54 x 70	1	320	Permanent	Paper
	Large Multi-Purpose Labels	2093094	32 x 57	6	1000	Permanent	Paper
	Large Multi-Purpose Labels	2093095	32 x 57	12	1000	Permanent	Paper
Specialty	Suspension File Labels	S0722460	12 x 50	1	220	Permanent	Paper
	Small Lever Arch File Labels	S0722470	38 x 190	1	110	Permanent	Paper
	Large Lever Arch File Labels	S0722480	59 x 190	1	110	Permanent	Paper
	Small Name Badge Labels	S0722560	41 x 89	1	300	Removable	Paper
	Appointment / Name Badge Cards	S0929100	51 x 89	1	300	Non-adhesive	Paper

LW Durable Labels

Tear-resistant, coated polypropylene labels with extra-strength adhesive that withstand abrasion, common cleaners, and a wide range of temperatures-ideal for shelving, storage, and signage.



Water



Solvents



Oil



Textured Surfaces



Temperature
-18°C to 50°C

Label Type	Description	Code #	Size (mm)	Rolls/Box	Labels/Roll	Adhesive	Material
Durable	LW Durable Labels	1933081	25 x 89	1	350	Permanent	Coated Polypropylene
	LW Durable Labels	1933083	25 x 25	2	850	Permanent	Coated Polypropylene
	LW Durable Labels	1933084	32 x 57	1	800	Permanent	Coated Polypropylene
	LW Durable Labels	1933085	19 x 64	2	450	Permanent	Coated Polypropylene
	LW Durable Labels (4XL only)	1933086	104 x 159	1	200	Permanent	Coated Polypropylene
	LW Durable Labels	1933087	59 x 190	1	170	Permanent	Coated Polypropylene
	LW Durable Labels	1933088	59 x 102	1	300	Permanent	Coated Polypropylene
	LW Durable Labels	1976411	25 x 54	1	160	Permanent	Coated Polypropylene

The DYMO® high quality labels are made in Belgium



© 2019 Newell Brands

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

