

OBO anchor



Hardened steel, shiny without thread.

Type	Shank length mm	Dimen- sion L mm	Dimen- sion D Ø mm	Pack. pcs	Weight kg/100 pcs.	Item No.
903 RB 15	15	21	4	200	0,295	3105016
903 RB 18	18	24	4	200	0,348	3105024
903 RB 22	22	30	4	200	0,325	3105032

St Steel

Dimensions

