

OBO anchor G



Hardened steel, electrogalvanised with M6 x 8 mm thread.

Type	Shank length mm	Dimension L mm	Dimension D Ø mm	Dimension G mm	Pack. pcs	Weight kg/100 pcs.	Item No.
903 15 G	15	23	4	M6	100	0,330	3100154
903 18 G	18	26	4	M6	100	0,360	3100189
903 25 G	25	33	4	M6	100	0,404	3100251
903 30 G	30	38	4	M6	100	0,470	3100308
903 40 G	40	48	4	M6	100	0,571	3100405

St Steel

G Electrogalvanised

Dimensions

