

HELUcond PA6-L Corrugated tubes, polyamide

Weak stress



HELUcond PA6-L

Cable protection tube for weak to medium stress applications.

Capacity/100mm NW 17: approx. 250 N

Application

- Plant and machine construction
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction

Material

Mod. Polyamide PA 6

Flammability acc. to UL 94: V2

- halogen-free
- phosphor-free

Properties

Resistant to a multitude of

- Fuels
- Mineral oils
- Greases
- Weak bases
- Weak acids

Note

Suitable connection glands:
HELUquick, HSSV.

Technical data

Temperature range: -40°C up to +120°C

Temperature range temporary up to +150°C

Fine profile

Part no. grey	Part no. black	Nominal size mm	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/100 metres at a purchase of		
						up to 100	101 - 500	501 - 1000
99610	99620	7,5	6,8	10,0	50	o. r.	o. r.	o. r.
99611	99621	10,0	10,0	12,8	50	o. r.	o. r.	o. r.
99612	99622	12,0	12,5	15,7	50	o. r.	o. r.	o. r.
99613	99623	14,0	14,4	18,5	50	o. r.	o. r.	o. r.
99614	99624	17,0	16,8	21,1	50	o. r.	o. r.	o. r.
99615	99625	23,0	23,4	28,4	50	o. r.	o. r.	o. r.
99616	99626	29,0	29,2	34,5	25	o. r.	o. r.	o. r.
99617	99627	37,0	34,0	41,8	25	o. r.	o. r.	o. r.
99618	99628	50,0	46,0	53,8	25	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request