

Product information

03 01 160

Combination Pliers

DIN ISO 5746

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General

Article No.	03 01 160
EAN	4003773013235
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	187 g
Dimensions	160 x 48 x 13 mm
Standard	DIN ISO 5746

Technische Attribute

Cutting capacities medium hard wire (diameter)	Ø 3.1 mm
Cutting capacities hard wire (diameter)	Ø 2.0 mm
Cutting capacity copper cable, multiple-stranded	Ø 10.0 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm ²

Classification

eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

technical change and errors excepted