

## Product information

### 34 12 130 ESD

#### Precision Electronics Gripping Pliers ESD

DIN ISO 9655 DIN EN 61 340-5



- The assortment for highest standard of performance and results
- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Bolted joint: precise, zero backlash operation of pliers
- Precisely finished joint surfaces for smooth, low friction movement along the complete opening range
- Low-friction double spring for gentle and even opening
- Smooth ground gripping surfaces, edges carefully deburred
- Non-reflective finish
- Low weight
- Ergonomically shaped, two-colour dual component ESD handles, black/grey
- Flat, wide jaws
- Ball bearing chrome steel, forged, multi stage oil-hardened

#### General

|             |                              |
|-------------|------------------------------|
| Article No. | 34 12 130 ESD                |
| EAN         | 4003773061632                |
| Pliers      | burnished                    |
| Head        | polished                     |
| Handles     | with multi-component grips   |
| weight      | 62 g                         |
| Dimensions  | 135 x 53 x 13 mm             |
| Standard    | DIN ISO 9655 DIN EN 61 340-5 |

#### Technische Attribute

|            |         |
|------------|---------|
| Style      | 1       |
|            | 21.9 mm |
|            | 6.5 mm  |
|            | 1.4 mm  |
|            | 3.5 mm  |
| Head width | 11.2 mm |
| ESD        | yes     |

#### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040301   |
| proficl@ss 6.0 | EAA840c015 |
| UNSPSC 13.1    | 27112149   |

technical change and errors excepted