

Product information

34 32 130

Precision Electronics Gripping Pliers

DIN ISO 9655



MM  8

- For very precise assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Smoothly ground gripping surfaces, edges finely rounded
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Round, pointed jaws
- Ball bearing chrome steel, forged, multi stage oil-hardened

General

Article No.	34 32 130
EAN	4003773061496
Pliers	burnished
Head	polished
Handles	with multi-component grips
weight	59 g
Dimensions	135 x 60 x 19 mm
Standard	DIN ISO 9655

Technische Attribute

Style	3
	23.7 mm
	6.5 mm
	2.0 mm
	1.0 mm
Head width	11.2 mm

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

technical change and errors excepted

