

Product information

35 32 115 ESD

Electronics Pliers ESD

DIN ISO 9655 DIN EN 61 340-5



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- With two-colour dual component grips, black/grey
- Round, pointed jaws
- Ball bearing chrome steel



General

Article No.	35 32 115 ESD
EAN	4003773024859
Head	mirror polished
Handles	with multi-component grips
weight	79 g
Dimensions	115 x 71 x 16 mm
Standard	DIN ISO 9655 DIN EN 61 340-5

Technische Attribute

Style	3
	22.5 mm
	6.5 mm
	2.0 mm
	1.0 mm
Head width	11.0 mm
ESD	yes

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

technical change and errors excepted

