

Product information

38 15 200

- High bending strength of the pliers tips
- Straight, half-round jaws
- Vanadium electric steel; forged, oil-hardened

Mechanics' Pliers

DIN ISO 5745



General

Article No.	38 15 200
EAN	4003773039594
Pliers	chrome plated
Head	chrome plated
Handles	with multi-component grips
weight	209 g
Dimensions	200 x 118 x 13 mm
Standard	DIN ISO 5745

Technische Attribute

Style	1
	9.5
	3.0 mm
	2.5 mm
	73.0 mm
Head width	17.5 mm

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAA004c004
UNSPSC 13.1	27112104

technical change and errors excepted