

Product information

38 25 200

- High bending strength of the pliers tips
- 40° bent, half-round jaws
- Vanadium electric steel; forged, oil-hardened

Mechanics' Pliers

DIN ISO 5745



General

Article No.	38 25 200
EAN	4003773043669
Pliers	chrome plated
Head	chrome plated
Handles	with multi-component grips
weight	209 g
Dimensions	200 x 52 x 19 mm
Standard	DIN ISO 5745

Technische Attribute

Style	2
	9.5
	3.0 mm
	2.5 mm
	73.0 mm
Head width	17.5 mm
	40

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAA004c004
UNSPSC 13.1	27112104

technical change and errors excepted