

Product information

44 31 J02

Circlip Pliers

For internal circlips in bore holes
45° bent

- Solid style, forged
- Non-slip, solid tips
- On basis of DIN 5256 C and DIN 5256 C, but bent 45°
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened



45°

General

Article No.	44 31 J02
EAN	4003773066941
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	103 g
Dimensions	140 x 48 x 11 mm

Technische Attribute

Style	3
Size of bore	Ø 8 – 13 mm
Tips (diameter)	Ø 0.9 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted