

Product information

44 31 J22

Circlip Pliers

For internal circlips in bore holes
45° bent

- Solid style, forged
- Non-slip, solid tips
- On basis of DIN 5256 C and DIN 5256 C, but bent 45°
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened



⌋45°

General

Article No.	44 31 J22
EAN	4003773066965
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	153 g
Dimensions	180 x 71 x 18 mm

Technische Attribute

Style	3
Size of bore	Ø 19 – 60 mm
Tips (diameter)	Ø 1.8 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted

