

Product information

70 05 160

Diagonal Cutter

DIN ISO 5749



- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With elongated cutting edge
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	70 05 160
EAN	4003773039600
Pliers	chrome plated
Head	chrome plated
Handles	with multi-component grips
weight	207 g
Dimensions	160 x 54 x 21 mm
Standard	DIN ISO 5749

Technische Attribute

Cutting capacities medium hard wire (diameter)	Ø 3.0 mm
Cutting capacities hard wire (diameter)	Ø 2 mm
Cutting capacities soft wire (diameter)	Ø 4.0 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted