

Product information

70 26 160

Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900



⚡ 1000 V 

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With elongated cutting edge
- With small bevel
- Vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	70 26 160
EAN	4003773018223
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	216 g
Dimensions	160 x 60 x 30 mm
Standard	DIN ISO 5749 DIN EN 60900 IEC 60900

Technische Attribute

Cutting capacities soft wire (diameter)	Ø 4.0 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted