

## Product information

# 71 21 200

## KNIPEX CoBolt®

### Compact Bolt Cutters



#### Clever muscle man

- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- 20° angled head with single-sided joint bar and diagonal cutting edge for flush cutting; with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



| General                                        |                    |
|------------------------------------------------|--------------------|
| Article No.                                    | 71 21 200          |
| EAN                                            | 4003773066866      |
| Pliers                                         | black atramentized |
| Handles                                        | plastic coated     |
| weight                                         | 334 g              |
| Dimensions                                     | 200 x 62 x 24 mm   |
| Technische Attribute                           |                    |
| Style                                          | 2                  |
| Cutting capacities medium hard wire (diameter) | Ø 5.2 mm           |
| Cutting capacities hard wire (diameter)        | Ø 4.0 mm           |
| Cutting capacities piano wire (diameter)       | Ø 3.6 mm           |
| Cutting capacities soft wire (diameter)        | Ø 6 mm             |
| Classification                                 |                    |
| eCl@ss 5.1.4                                   | 21040302           |
| ETIM 5.0                                       | EC002689           |
| ETIM 6.0                                       | EC002689           |
| proficl@ss 6.0                                 | AAC440c002         |
| UNSPSC 13.1                                    | 27111512           |

technical change and errors excepted

