

Product information

78 61 140 ESD

- Precision shaped tips cut wires flush to a surface from Ø 0.2 mm.
- Special tool steel, oil hardened in multiple stages

Electronic Super Knips® XL ESD

DIN ISO 9654 DIN EN 61 340-5



General

Article No.	78 61 140 ESD
EAN	4003773081708
Pliers	burnished
Head	burnished
Handles	with multi-component grips
weight	93 g
Dimensions	140 x 50 x 48 mm
Standard	DIN ISO 9654 DIN EN 61 340-5

Technische Attribute

Cutting capacities medium hard wire (diameter)	Ø 1.4 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 2.1 mm
	12.3 mm
	9.2 mm
Head width	15.7 mm
ESD	yes

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112149

technical change and errors excepted