

## Product information

**87 03 250**

**KNIPEX Cobra®**

Hightech Water Pump Pliers

DIN ISO 8976

- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened



### General

|             |                               |
|-------------|-------------------------------|
| Article No. | 87 03 250                     |
| EAN         | 4003773043805                 |
| Pliers      | chrome plated                 |
| Head        | chrome plated                 |
| Handles     | with non-slip plastic coating |
| weight      | 335 g                         |
| Dimensions  | 250 x 60 x 14 mm              |
| Standard    | DIN ISO 8976                  |

### Technische Attribute

|                                 |         |
|---------------------------------|---------|
| Adjustment positions            | 25      |
| Capacities for nuts             | Ø 2     |
| Capacities for nuts             | 46 mm   |
| Capacities for pipes (diameter) | Ø 50 mm |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040301   |
| ETIM 5.0       | EC000164   |
| ETIM 6.0       | EC000164   |
| proficl@ss 6.0 | AAA936c004 |
| UNSPSC 13.1    | 27112112   |

technical change and errors excepted



