

Product information

97 68 145 A

Crimping Pliers for wire ferrules

IEC 60900 DIN EN 60900

- For crimping wire ferrules according to DIN 46228 parts 1 + 4 in the range from 0.25 up to 2.5 mm²
- Crimping in marked trapezoidal dies for reliable connections between the sleeve and the conductor
- Vanadium electric steel; forged, oil-hardened



1000 V   

General

Article No.	97 68 145 A
EAN	4003773071754
Head	polished
Handles	insulated with multi-component grips, VDE-tested
weight	190 g
Dimensions	145 x 60 x 25 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute

Applications	Wire ferrules
Capacity in square millimetres	0.25 — 2.5 mm ²
Number of crimping positions	4
AWG	23 — 13

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted