

Product information

98 03 055

Nut Driver

With screwdriver handle

IEC 60900 DIN EN 60900

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000 V ⚡

General

Article No.	98 03 055
EAN	4003773026082
Pliers	burnished
Handles	insulating multi-component handle, VDE-tested
weight	87 g
Dimensions	232 x 123 x 27 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute

Width across flats S	5.5 mm
Handle length max.	107 mm
Head dia.	11 mm
Blade length	125 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040206
ETIM 5.0	EC000174
ETIM 6.0	EC000174
proficl@ss 6.0	AAA891c007
UNSPSC 13.1	27111702

technical change and errors excepted