

Product information

98 20 65 SL

Screwdriver (Slim) for slotted screws

IEC 60900 DIN EN 60900

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000V 

Allgemein

Article No.	98 20 65 SL
EAN	4003773079743
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	117 g
Dimensions	262 x 123 x 32 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute

Blade length	150 mm
Length of non-insulated blade	15 mm
Handle length	112 mm
Blade width	6.5 mm
Blade thickness	1.2 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040401
ETIM 5.0	EC000158
ETIM 6.0	EC000158
proficl@ss 6.0	AAA817c008
UNSPSC 13.1	27111701

technical change and errors excepted