

Product information

98 53 13

Stripping Knives

IEC 60900 DIN EN 60900

- Ergonomically designed handle shape with comfortable slip guard
- Particularly confident grip thanks to slip-proof soft components
- Thumb recess and "finger hook" at the end of the handle ensure a good transmission of force when the blade is pulled
- Transparent protective cap
- Narrow, fixed hook blade, sickle shaped
- Suitable for sector cables
- Blade: special tool steel, oil-hardened



⚡ 1000 V

General

Article No.	98 53 13
EAN	4003773026556
Handles	insulating multi-component handle, VDE-tested
weight	88 g
Dimensions	190 x 118 x 52 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute

Blade length	50 mm
Radius	40 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040602
ETIM 5.0	EC000155
ETIM 6.0	EC000155
proficl@ss 6.0	EAB554c020
UNSPSC 13.1	23241609

technical change and errors excepted