

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2002180200

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 22 AWG, Large and Small Insulation Grips

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Fit TPA2
Tool Type	Hand Crimp Tool
UPC	889056764452
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-2002180200-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Application Tooling Description	FAQ Product #
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Reel	1727185111
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Bag	1727185112
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Brass, Pre-Plated	1727185121

	Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727185122</u> Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727186111</u> Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727186112</u> Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727186121</u> Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727186122</u> Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727655121</u> Sigma Male Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727655122</u> Sigma Male Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727656121</u> Sigma Male Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG,
--	--

	1.65-2.38mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727656122</u> Sigma Male Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>2029885141</u> Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>2029885142</u> Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>2029885241</u> Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>2029885242</u> Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>2029886141</u> Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>2029886142</u> Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>2029886241</u> Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm
--	---

Insulation Diameter, Reel	
Mini-Fit TPA2/	<u>2029886242</u>
Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Bag	
Mini-Fit TPA2/	<u>2030705141</u>
Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Reel	
Mini-Fit TPA2/	<u>2030705142</u>
Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.07-1.65mm Insulation Diameter, Loose	
Mini-Fit TPA2/	<u>2030706141</u>
Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Reel	
Mini-Fit TPA2/	<u>2030706142</u>
Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Loose	