

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2002181700

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 16 AWG, Large and Small Insulation Grips

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Fit TPA2
Tool Type	Hand Crimp Tool
UPC	191128448642
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents2002181700-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

207129 Series

Application Tooling Description	FAQ Product #
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	1727181111
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag	1727181112
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 16 AWG, 1.98-2.55mm	1727181121

	Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727181122</u> Sigma Female Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727182111</u> Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 16 AWG, 2.55-3.14mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727182112</u> Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 16 AWG, 2.55-3.14mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727182121</u> Sigma Female Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 2.55-3.14mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727182122</u> Sigma Female Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 2.55-3.14mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727651121</u> Sigma Male Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727651122</u> Sigma Male Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag Mini-Fit TPA2/ <u>1727652121</u> Sigma Male Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 2.55-3.14mm Insulation Diameter, Reel Mini-Fit TPA2/ <u>1727652122</u> Sigma Male Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 2.55-3.14mm
--	--

Insulation Diameter, Bag	
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2029881141</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag	<u>2029881142</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2029881241</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag	<u>2029881242</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2030701141</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2030701241</u>