

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018671

Status:

Active

Overview:

Application Tooling

Description:

Vertical Receptacle Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207122
Comments	See Tooling Specification (PDF) Above, Press-In Tool
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	883906174811
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018671



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207122 Series

Use With

LPH Vertical Receptacle 46114 Series

Application Tooling Description	FAQ Product #
1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	461141020
1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	461141021

	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141024</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141025</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141028</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141029</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141040</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141041</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141220</u>

	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141221</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141224</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141225</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141228</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141229</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141240</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant	<u>461141241</u>

	Pin, 12 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm <u>461141420</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm <u>461141421</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm <u>461141424</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm <u>461141425</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm <u>461141428</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm <u>461141429</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, without BMI Guides
--	---

	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141440</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141441</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461142200</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461142201</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461142240</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461142241</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461142280</u>

	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461142281</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461142400</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461142401</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 4 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461144200</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 4 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461144201</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 4 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461144240</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 4 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461144241</u>
	1.27mm, 12.00mm Pitch, EXTreme	<u>461144280</u>

LPHPower Receptacle Header, Vertical, 4 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461144281</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 4 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461144400</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 4 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461144401</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 4 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461146200</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461146201</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461146240</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461146241</u>
Pitch, EXTreme LPHPower Receptacle Header,	

Vertical, 6 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	
1.27mm, 12.00mm	<u>461146280</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	
1.27mm, 12.00mm	<u>461146281</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	
1.27mm, 12.00mm	<u>461146400</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	
1.27mm, 12.00mm	<u>461146401</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	
1.27mm, 12.00mm	<u>461148200</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	
1.27mm, 12.00mm	<u>461148201</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	
1.27mm, 12.00mm	<u>461148240</u>
Pitch, EXTreme LPHPower Receptacle Header,	

Vertical, Compliant Pin, 8 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm Pitch, EXTreme LPHPower	<u>461148241</u>
Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm Pitch, EXTreme LPHPower	<u>461148280</u>
Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm Pitch, EXTreme LPHPower	<u>461148400</u>
Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm Pitch, EXTreme LPHPower	<u>461148401</u>
Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 40 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	

This document was generated on 01/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION