

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018672

Status:

Active

Overview:

Application Tooling

Description:

Vertical Receptacle Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207122

See Tooling Specification (PDF) Above, Press-In Tool

Insertion

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Press-Fit Insertion Tool

883906174828

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

38.900/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018672



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207122 Series

Use With

LPH Vertical Receptacle 46114 Series

Application Tooling Description	FAQ Product #
1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	461141012
1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	461141013

	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141016</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141017</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141032</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141033</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141036</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141037</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141212</u>

	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141213</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141216</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141217</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141232</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141233</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141236</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant	<u>461141237</u>

	Pin, 12 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm <u>461141412</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm <u>461141413</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm <u>461141416</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm <u>461141417</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm <u>461141432</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm <u>461141433</u> Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	
--	---	--

	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461141436</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 14 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461141437</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461142120</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461142121</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461142160</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, without BMI Guides	<u>461142161</u>
	1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, with BMI Guides	<u>461142320</u>

	1.27mm, 12.00mm	461142321
	Pitch, EXTreme	
	LPHPower	
	Receptacle Header,	
	Vertical, 2 Power	
	Contacts, 32 Signal	
	Contacts, Select	
	Gold (Au) Plating,	
	without BMI Guides	
	1.27mm, 12.00mm	461142360
	Pitch, EXTreme	
	LPHPower	
	Receptacle Header,	
	Vertical, 2 Power	
	Contacts, 36 Signal	
	Contacts, Select	
	Gold (Au) Plating,	
	with BMI Guides	
	1.27mm, 12.00mm	461142361
	Pitch, EXTreme	
	LPHPower	
	Receptacle Header,	
	Vertical, 2 Power	
	Contacts, 36 Signal	
	Contacts, Select	
	Gold (Au) Plating,	
	without BMI Guides	
	1.27mm, 12.00mm	461144120
	Pitch, EXTreme	
	LPHPower	
	Receptacle Header,	
	Vertical, 4 Power	
	Contacts, 12 Signal	
	Contacts, Select	
	Gold (Au) Plating,	
	with BMI Guides	
	1.27mm, 12.00mm	461144121
	Pitch, EXTreme	
	LPHPower	
	Receptacle Header,	
	Vertical, 4 Power	
	Contacts, 12 Signal	
	Contacts, Select	
	Gold (Au) Plating,	
	without BMI Guides	
	1.27mm, 12.00mm	461144160
	Pitch, EXTreme	
	LPHPower	
	Receptacle Header,	
	Vertical, 4 Power	
	Contacts, 16 Signal	
	Contacts, Select	
	Gold (Au) Plating,	
	with BMI Guides	
	1.27mm, 12.00mm	461144161
	Pitch, EXTreme	
	LPHPower	
	Receptacle Header,	
	Vertical, 4 Power	
	Contacts, 16 Signal	
	Contacts, Select	
	Gold (Au) Plating,	
	without BMI Guides	
	1.27mm, 12.00mm	461144320
	Pitch, EXTreme	

	LPHPower Receptacle Header, Vertical, 4 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm 461144321 Pitch, EXTreme
	LPHPower Receptacle Header, Vertical, 4 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm 461144360 Pitch, EXTreme
	LPHPower Receptacle Header, Vertical, 4 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm 461144361 Pitch, EXTreme
	LPHPower Receptacle Header, Vertical, 4 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm 461146120 Pitch, EXTreme
	LPHPower Receptacle Header, Vertical, 6 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm 461146121 Pitch, EXTreme
	LPHPower Receptacle Header, Vertical, 6 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm 461146160 Pitch, EXTreme
	LPHPower Receptacle Header, Vertical, 6 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm 461146161 Pitch, EXTreme
	LPHPower Receptacle Header,

Vertical, 6 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461146320</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461146321</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461146360</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461146361</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461148120</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 12 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461148121</u>
Pitch, EXTreme LPHPower Receptacle Header,	

Vertical, Compliant Pin, 8 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461148161</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461148320</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461148321</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 32 Signal Contacts, Select Gold (Au) Plating, without BMI Guides 1.27mm, 12.00mm	<u>461148360</u>
Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 8 Power Contacts, 36 Signal Contacts, Select Gold (Au) Plating, with BMI Guides 1.27mm, 12.00mm	<u>461148361</u>