

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638132500

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for 2.80mm CP Crimp Terminals for CMC connector

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207121

<p style=""margin-top: 0; marginbottom: 0">See Tooling Specification (PDF) Above<p style=""margin-top: 0; marginbottom: 0">Extraction Tool for removal of 98910 Series

Extraction

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Extraction Hand Tool

800756720227

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

3.000/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638132500, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Not Reviewed

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
2.80mm, CMC CP Female Terminal, Tin plated, for Tab Dimensions 2.80mm by 0.80mm, Wire Size > 3.00-5.00mm²	643241019
2.80mm, CMC CP Female Terminal, Tin plated, for Tab Dimensions 2.80mm by 0.80mm, Wire Size > 2.00-3.00mm²	643241029
2.80mm, CMC CP Female Terminal, Tin plated, for Tab Dimensions 2.80mm by 0.80mm, Wire Size > 1.00-2.00mm²	643241039
2.80mm, CMC CP Female Terminal, Tin plated, for Tab Dimensions 2.80mm	643241049

by 0.80mm, Wire
Size 0.50-1.00mm²
2.80mm, CMC CP [643241119](#)
Female Terminal,
Tin plated; Selective
1.27μm Gold in
Contact Area, for
Tab Dimensions
2.80mm by 0.80mm,
Wire Size >
3.00-5.00mm²
2.80mm, CMC CP [643241129](#)
Female Terminal,
Tin plated; Selective
1.27μm Gold in
Contact Area, for
Tab Dimensions
2.80mm by 0.80mm,
Wire Size >
2.00-3.00mm²
2.80mm, CMC CP [643241139](#)
Female Terminal,
Tin plated; Selective
1.27μm Gold in
Contact Area, for
Tab Dimensions
2.80mm by 0.80mm,
Wire Size >
1.00-2.00mm²
2.80mm, CMC CP [643241149](#)
Female Terminal,
Tin plated, Selective
1.27μm Gold in
Contact Area, for
Tab Dimensions
2.80mm by
0.80mm, Wire Size
0.50-1.00mm²