

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638687000](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for iGrid Receptacle Terminals, 22-26 AWG with Insulation
Diameter 0.95-1.50mm UL1007 wire

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207127](#)
Comments See Tooling Specification (PDF) Above, Terminals will accommodate the UL1007 wires

Function Crimp
Geographic Area Global
Level of Automation Automatic, Semi-Automatic
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name FineAdjust
Tool Type Applicator
UPC 822350861090
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 4996.288/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents
ATS-638687000, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Relevant
For more information, please visit [Contact US](#)

China ROHS Not Relevant
ELV Not Relevant
RoHS Phthalates Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#)
 , Molex TM-4000: [638017600](#) , Molex
TM-2000: [638008300](#) , [638008400](#) , and
Most Industry Standard Presses or Wire
Process Machines

Application Tooling Description	FAQ Product #
2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Reel	5016471000