

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639015600

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for 18-20 AWG and 18-24 AWG Wires with Insulation Diameter 1.90-2.30mm

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207127

See Tooling Specification (PDF) Above

Crimp

Global

Automatic, Semi-Automatic

applicationtooling@molex.com

Application Tooling

FineAdjust

Applicator

884982036659

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

4985.136/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-639015600, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE, TM-638004900FR, TM-638004900IT, TM-638004900JP, TM-638004900KR, TM-638004900MY, TM-638004900PL, TM-638004900RU, TM-638004900SK, TM-638004900SP-001, TM-638004900TH, TM-638004900TW, TM-638004900VN



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Mini-Fit Jr. Grounding Pin, 18-24 AWG, Reel, Phosphor Bronze, Tin or Select Gold (Au)	304901002
Mini-Fit Jr. Crimp Grounding Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18-24 AWG, Reel	304902002
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper	39000038

(Cu) Plated Brass, 18-24 AWG, Reel	
Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Reel	<u>390000040</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel	<u>390000059</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel	<u>390000061</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel	<u>390000073</u>
Mini-Fit Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 18-24 AWG, Reel	<u>390000075</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	<u>390000120</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag	<u>390000121</u>
Mini-Fit Male Crimp Terminal, Tin (Sn), Phosphor Bronze, 18-24 AWG, Reel	<u>390000126</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) over Phosphor Bronze, 18-24 AWG, Reel	<u>390000181</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel	<u>390000207</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel	<u>390000213</u>
Mini-Fit Male Crimp Terminal, Phosphor Bronze, Gold (Au), 18-24 AWG, Reel	<u>390000219</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au)	<u>390000428</u>

and Selective Tin
(Sn) over Nickel (Ni),
18-24 AWG, Reel
Mini-Fit Male Crimp 39000430
Terminal, Brass,
Gold (Au) Contact
Plating, Lead-free,
18-24 AWG, Reel
Mini-Fit Plus Crimp 457501111
Terminal, 18-20
AWG, Reel, Copper
(Cu) Alloy, Tin (Sn)
Mini-Fit Plus Crimp 457501211
Terminal, 18-20
AWG, Reel, Copper
(Cu) Alloy, Gold (Au)
Selective
Mini-Fit Plus Crimp 460121141
Terminal, 18-20
AWG, Reel, Tin (Sn)
Plating
Mini-Fit Plus Crimp 460121241
Terminal, 18-20
AWG, Reel, 0.76µm
Selective Gold (Au)
Plating
Mini-Fit Plus High 460181541
Mating Cycle Female
Crimp Terminal,
18-20 AWG,
Reel, Select Gold
(Au) Plating with
Proprietary Molex
Advanced Contact
Surface Finish (CSF)
in Contact Area