

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639009800](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for Crimp Terminals, 14-20 AWG Wire with 2.65-3.30mm Diameter Insulation

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207127](#)
Comments See Tooling Specification (PDF) Above
Function Crimp
Geographic Area Global
Level of Automation Automatic, Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview [Application Tooling](#)
Product Name FineAdjust
Tool Type Applicator
UPC 883906267049
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 4986.951/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents
ATS-639009800, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
MLX Female Crimp Terminal 42024, 14-20 AWG, Reel, Brass, Tin (Sn) Plating	2081001
MLX Female Crimp Terminal 42024, 14-20 AWG, Reel, Phosphor Bronze, Tin (Sn) Plating	2081003
MLX Male Crimp Terminal 42023, 14-20 AWG, Reel, Brass, Tin (Sn) Plating	2082003

MLX Male Crimp Terminal 42023, 14-20 AWG, Reel, Phosphor Bronze, Tin (Sn) Plating	<u>2082005</u>
---	----------------

This document was generated on 02/10/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION