

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639023200](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for SL Crimp Terminals, for 22-24 AWG Wire with Insulation Diameter 1.40-1.63mm

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207127](#)
Comments See Tooling Specification (PDF) Above, Terminals will accommodate the UL1007 wires

Function Crimp
Geographic Area Global
Level of Automation Automatic, Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview [Application Tooling](#)
Product Name FineAdjust
Tool Type Applicator
UPC 884982667082
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 5080.445/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents
ATS-639023200, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free Status
Not Relevant
For more information, please visit [Contact US](#)

China ROHS Not Relevant
ELV Not Relevant
RoHS Phthalates Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
SL Crimp Terminal, Series 70058, Female, 22-24 AWG, with Tin (Sn) Plated Contact, Reel	16020086
SL Crimp Terminal, Series 70058, Female, 22-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	16020087
SL Crimp Terminal, Series 70058, Female, 22-24 AWG, with 0.76µm	16020088

Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, 16021110
Series 71851,
Female, with Tin
(Sn) Plated Contact,
22-24 AWG, Reel
SL Crimp Terminal, 16021111
Series 71851,
Female, with 0.76µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Reel
SL Crimp Terminal, 16021124
Series 71851,
Female, with 0.38µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Reel
SL Crimp Terminal, 700580087
Female, 22-24
AWG, with 0.38µm
Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, 700580088
Female, 22-24
AWG, with 0.76µm
Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, 700584086
Series 70058,
Female, 22-24 AWG,
with Tin (Sn) Plated
Contact, Unplated
Edges, Reel

This document was generated on 02/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION