

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639025800

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for Micro-Fit 3.0 and Micro-Fit Plus Terminals, for 0.75mm² and 18 AWG (UL1061) Wires with Insulation Diameter 1.40-1.85mm

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	887191653440
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-639025800-001, TM-638000029-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Micro-Fit High-Current RMF Crimp Terminal, Female, 2.540µm Bright Tin Plating, 18 AWG	2039510001
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 18 AWG	2064600031
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in /	430300038

1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in /	<u>430300039</u>
1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0 Crimp Terminal, Female, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in /	<u>430300040</u>
1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in /	<u>430310021</u>
1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in /	<u>430310022</u>
1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in /	<u>430310023</u>
1.85mm Max Insulation Outside Diameter, Reel	