

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640031100

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822348637232
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

RHT-1751

Reference - Drawing Numbers

Application Tooling Documents

ATS-640031100, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.51mm	190160001
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.81mm	190160003
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 4.75 x 0.51mm	190160005

	Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190160009</u>
	Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 2.79 x 0.51mm	<u>190160035</u>
	Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 2.79 x 0.81mm	<u>190160037</u>
	Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 4.75 x 0.51mm	<u>190160039</u>
	Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 4.75 x 0.81mm	<u>190160040</u>
	Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190160111</u>
	Krimptite Snap Plug Receptacle, for 18-22 AWG Wire, Box, 16.26mm Length	<u>190370002</u>
	Krimptite Snap Plug Receptacle, for 14-16 AWG Wire, Box, 16.26mm Length	<u>190370004</u>
	Krimptite Snap Plug Receptacle, for 14-16 AWG Wire, Box, 17.80mm Length	<u>190370006</u>
	Krimptite Snap Plug Receptacle, for 18-22 AWG Wire, Box, 17.80mm Length	<u>190370015</u>
	Krimptite Quick Disconnect, Female, Steel, 483°C (900° F), 14-16 AWG, Tab 6.35mm	<u>192030390</u>
	Quixon Quick Disconnect, Krimptite Style, Female, Un-	<u>192730007</u>

insulated, 18-20
AWG, Loose
Quixon Quick 192730008
Disconnect, Krimptite
Style, Female, Un-
insulated, 14-16
AWG, Loose

This document was generated on 02/11/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION