





Revision Level		Revision Record	Changed	Date	Approval	Date
Part	Drawing					



G (Flat Length)



Delivery Conditions



A	B	G
1.3 ±0.2	4.6 ±0.2	150 ±5.0

Clamp TE4-511-000-K FIT FOR MATERIAL THICKNESS 1 ~ 3mm.

Material
P.A. 66
Tensile strength
225N (Minimum)
Tolerances
PERFORMANCE SPECIFICATION

ACAD	Drawn Simon Ng 30 May 2018	Scale: 1 : 1	Reference: NT371-02
	Approved. EDWARD TAN 30 May 2018	Title T50SOSEC9SD	Drawing-No [SG18002-00] 02-0371-001-CSH
The copyright of this drawing is reserved by HELLERMANNTYTON. It is issued on condition that it is not reproduced, copied or disclosed to a third party, either wholly or in part, without the consent of HELLERMANNTYTON.		HellermannTyton 545, Yishun Industrial Park A Yishun Avenue 7 Singapore 768741 Tel: (+65) 6852 8585 Fax: (+65) 6756 6798	
		Format A4	Sheet 1 of 1

Uncontrolled Document