

CATIA V5

Material
Matière
Werkstoff

Messing, vernickelt/
Brass, nickel plate

Dichtung/Seal:
PA6

Tolerances
Dimension without tolerances:
Tolérances
Cotes sans tolérances:
Toleranzen
Masse ohne
Toleranzangaben :

Angle/ Winkel

± 3°

≤ 6

± 0,3

≤ 30

± 0,5

≤ 60

± 0,7

≤ 120

± 1,5


≤ 400

± 5

≤ 1000

± 10

PERFORMANCE
SPECIFICATION
AUSFUEHRUNG
SPEZIFIKATION



Alle Masze haben ausschliesslich informativen Charakter/All dimensions are for information purposes only

Artikelbezeichnung/ Product type	Nom. Schlauch-Ø/ Nom. Conduit-Ø	Gewinde/Thread L	M	N	SW / A/F O	Lichte Weite/Bore P	SW / A/F R	Projektnr./ Project no.
LTS10-FMC-M12	10	M12x1.5	10	19.8	20	5.6	20	GPN 10-0947
LTS10-FMC-M16	10	M16x1.5	10	19.8	20	5.6	20	GPN 10-0948
LTS12-FMC-M16	12	M16x1.5	10	19.8	22	8.6	20	GPN 10-0950
LTS16-FMC-M16	16	M16x1.5	12	21.0	26	10.7	24	GPN 10-0951
LTS16-FMC-M20	16	M20x1.5	12	21.0	26	10.7	24	GPN 10-0952
LTS20-FMC-M20	20	M20x1.5	12	21.5	29	14.5	26	GPN 10-0953
LTS25-FMC-M25	25	M25x1.5	14	26.5	35	18.0	33	GPN 10-0954
LTS32-FMC-M32	32	M32x1.5	15	30.8	42	24.6	40	GPN 10-0955
LTS40-FMC-M40	40	M40x1.5	16	31.5	52	32.7	50	GPN 10-0956
LTS50-FMC-M50	50	M50x1.5	18	35.0	58	37.7	58	GPN 10-0957
LTS63-FMC-M63	63	M63x1.5	20	38.8	70	49.0	70	GPN 10-0958
LTS16-FMC-PG11	16	PG11	10	21.0	26	10.7	24	GPN 10-0959
LTS20-FMC-PG16	20	PG16	11	21.5	29	14.5	26	GPN 10-0960
LTS25-FMC-PG21	25	PG21	12	26.5	35	18.0	33	GPN 10-0961
LTS32-FMC-PG29	32	PG29	12	30.8	42	24.6	40	GPN 10-0962

mit integrierter Dichtung (bildlich nicht dargestellt)/
with integrated seal (not visually represented)

Ausdruck nur zur Information /
Printed copy for information only

The copyright of this drawing is reserved by HELLERMANN TYTON. It is issued on condition that it is not reproduced, copied or disclosed to a third party, either wholly or in part, without the consent of HELLERMANN TYTON.

La propriété de ce plan est réservée à la société HELLERMANN TYTON. Il est distribué à condition qu'il ne soit pas reproduit, communiqué ou révélé à une tierce partie, soit complètement ou en partie, sans le consentement de la société HELLERMANN TYTON.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte fuer den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

Drawn
Dessiné Par
Gezeichnet

Approved
Approuvé Par
Geprueft

Manchester

Trappes

Tornesch

Langeloh

Schiwek

04.11.10

04.11.10

Scale
Echelle
Maszstab

Title
Titre
Benennung

Drawing-No
Plan-No
Zeichnungs-Nr

Project Number
Numéro de projet
Projektnummer

Format
D.Size

Sheet
Page
Blatt

Siehe Tabelle/
See table

LTS...-FMC...
Verschraubung/Fitting

10-0947-001-CSG

A3
1 / 1

Telephone: +44 (0) 161 945 4181
Facsimile: +44 (0) 161 947 2228

Téléphone: +33 (0) 1 30 13 80 00
Télécopie: +33 (0) 1 30 13 80 60

Telefon: +49 (0) 41 22 / 701 - 1
Telefax: +49 (0) 41 22 / 701 - 400