

Product information

76 12 125

Diagonal Cutter

For electromechanics

DIN ISO 5749

- With sharp, precisely aligned cutting edges for soft, hard wire and piano wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- Lap joint
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	76 12 125
EAN	4003773048015
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
weight	112 g
Dimensions	125 x 60 x 19 mm
Standard	DIN ISO 5749

Technische Attribute

Style	1
Cutting capacities medium hard wire (diameter)	Ø 2.3 mm
Cutting capacities hard wire (diameter)	Ø 1.5 mm
Cutting capacities soft wire (diameter)	Ø 0.4 – 3 mm
	16 mm
	9 mm
Head width	14.5 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted