

Product information

02 05 225

High Leverage Combination Pliers

DIN ISO 5746

- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- Cutter head: special high-grade tool steel, forged, oil-hardened



General

Article No.	02 05 225
EAN	4003773010005
Pliers	chrome plated
Head	chrome plated
Handles	with multi-component grips
weight	418 g
Dimensions	225 x 51 x 21 mm
Standard	DIN ISO 5746

Technische Attribute

Cutting capacities hard wire (diameter)	Ø 3.0 mm
Cutting capacities piano wire (diameter)	Ø 2.5 mm
Cutting capacity copper cable, multiple-stranded	Ø 14.0 mm
Cutting capacity copper cable, multiple-stranded	25.0 mm ²

Classification

eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

technical change and errors excepted

