

Product information

03 07 180

Combination Pliers

DIN ISO 5746 IEC 60900 DIN EN 60900

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General

Article No.	03 07 180
EAN	4003773015314
Pliers	chrome plated
Head	chrome plated
Handles	with dipped insulation, VDE-tested
weight	285 g
Dimensions	180 x 65 x 40 mm
Standard	DIN ISO 5746 DIN EN 60900 IEC 60900

Technische Attribute

Cutting capacities medium hard wire (diameter)	Ø 3.4 mm
Cutting capacities hard wire (diameter)	Ø 2.2 mm
Cutting capacity copper cable, multiple-stranded	Ø 12.0 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm ²
VDE tested	yes

Classification

eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

technical change and errors excepted