

Product information

22 06 160

Round Nose Pliers

DIN ISO 5745 IEC 60900 DIN EN 60900

- For bending wire loops
- Round, short jaws; finely ground
- Smooth tips
- Special tool steel, forged, oil-hardened



⚡ 1000V 

General

Article No.	22 06 160
EAN	4003773033790
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	175 g
Dimensions	160 x 48 x 30 mm
Standard	DIN ISO 5745 DIN EN 60900 IEC 60900

Technische Attribute

	9.5 mm
	3.0 mm
	30.0 mm
Head width	18 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000834
ETIM 6.0	EC000834
proficl@ss 6.0	AAA005c004
UNSPSC 13.1	27112125

technical change and errors excepted

